



BUSINESS PRODUCTIVITY MONITOR  
**PRO MP241CA**  
PRO MP241CA

## Be Your Window To The World



Picture and logos

### SELLING POINTS

- 1500R curvature brings the most immersive viewing experience for your work & amusement.
- TÜV certified display protects your eyesight and keeps your eyes healthy
- Anti-Flicker and Less Blue Light technologies prevent your eyes from strain & fatigue
- Ergonomic software, Display Kit, provides the most convenient tool, the proper color & display mode to you while working with it everyday
- 75 Hz refresh rate provides a better viewing experience
- Keep the flexibility for your different devices with multiple input sources: HDMI & DP ports
- Standard VESA mountable design
- Always allow you to join an online conference call with built-in speakers



1. 1x DP (1.2a)
2. 1x HDMI (1.4b)
3. 1x Headphone-out
4. 1x Kensington Lock
5. 5x OSD Button



## SPECIFICATION

Barcode Info	EAN	4719072977276
	UPC	824142294710
	UCC14	10824142294717
Model	Part No	9S6-3PA9CT-007
	MKT Name	PRO MP241CA
	MKT Spec	PRO MP241CA
Display	Color	ID1/Black-Black
	Screen Size	23.6" (60cm)
	Active Display Area (mm)	521.3952(H)x293.2848(V)
	Curvature	Curve 1500R
	Panel Type	VA
	Resolution	1920x1080 (FHD)
	Aspect Ratio	16:9
	Dynamic Refresh Rate technology	FreeSync
	HDR (High dynamic range)	N/A
	SDR Brightness (nits)	250
	Contrast Ratio	3000:1
	DCR (Dynamic Contrast Ratio)	100000000:1
	Signal Frequency	52.8~90 KHz(H) / 48~75 Hz(V)
	Refresh Rate	75Hz
	Response Time (MPRT)	1ms(MPRT)
	Response Time (Tr + Tf)	N/A
	View Angles	178°(H)/178°(V)
	Surface Treatment	Anti-glare
	NTSC (CIE1976 area percentage/overlap)	99.78%/85.50%
	NTSC (CIE1931 area percentage/overlap)	84.64%/79.15%
	sRGB (CIE1976 area percentage/overlap)	114.44%/98.46%
	sRGB (CIE1931 area percentage/overlap)	119.50%/99.60%
	Adobe RGB (CIE1976 area percentage/overlap)	98.07%/89.38%
	Adobe RGB (CIE1931 area percentage/overlap)	88.57%/83.20%
	DCI-P3 (CIE1976 area percentage/overlap)	91.14%/90.94%
	DCI-P3 (CIE1931 area percentage/overlap)	88.09%/87.97%
	Rec.709 (CIE1976 area percentage/overlap)	114.44%/98.46%
	Rec.709 (CIE1931 area percentage/overlap)	119.50%/99.60%
	Rec.2020 (CIE1976 area percentage/overlap)	66.41%/66.41%
	Rec.2020 (CIE1931 area percentage/overlap)	63.20%/63.20%
	Display Colors	16.7M
	Color bit	8 bits
	Note_DP	1920 x 1080 (Up to 75Hz)
	Note_HDMI™	1920 x 1080 (Up to 75Hz)
	Note_DVI	N/A
I/O Ports	HDMI™	1
	HDMI™ version	1.4b
	HDMI™ HDCP version	1.4
	DisplayPort	1
	DisplayPort version	1.2a
	DisplayPort HDCP version	1.3
	Headphone-out	1
	Lock type	Kensington Lock
	Speaker	2
Power	Annual Energy Consumption (KWh)	N/A
	Power Supply Type	Power Cable
	Power Input	100~240V, 50/60Hz
	Adapter's KC safety Number	N/A
	Power Cord Type	C13
	QC Output Power	N/A
	PD Output Power	N/A



In The Box	3.5mm Mic Cable	0
	Switch Case	0
	Portable Screen Protection Case	0
	Monitor Hood	0
	Speaker (Accessories)	0
	DisplayPort Cable	0
	HDMI™ Cable	1
	DVI Cable	0
	USB Type A to Type B Cable	0
	USB Type C to Type A Cable	0
	USB Type C to Type C Cable	0
	Thunderbolt Cable	0
	VGA Cable	0
	3.5mm audio Cable	0
	3.5mm combo audio Cable	0
	Mouse Bungee Unit	0
	VESA Screw	0
	Power Cord	1
	AC Adaptor	0
	Warranty Card	0
	Quick Guide	1
Pallet	pcs/Carton	N/A
Design	Adjustment (Tilt)	-3.5° ~ 21.5°
	VESA Mounting	100x100mm
	Frameless Design	Yes
Outer Carton Dimension (WxDxH)	Outer Carton Dimension (WxDxH) (mm)	615 x 179 x 436
	Outer Carton Dimension (WxDxH) (inch)	24.21 x 7.05 x 17.17
Product Dimension with Stand (WxDxH)	Product Dimension with Stand (WxDxH) (mm)	536.9 x 237 x 407.4
	Product Dimension with Stand (WxDxH) (inch)	21.14 x 9.33 x 16.04
Product Dimension without Stand (WxDxH)	Product Dimension without Stand (WxDxH) (mm)	536.9 x 67.3 x 322.9
	Product Dimension without Stand (WxDxH) (inch)	21.14 x 2.65 x 12.71
Stand Dimension (WxDxH)	Stand Dimension (WxDxH) (mm)	237 x 240 x 157
	Stand Dimension (WxDxH) (inch)	9.33 x 9.45 x 6.18
Dimension & Weight	Inside Carton Dimensions (WxDxH) (mm)	600 x 164 x 411
	Inside Carton Dimensions (WxDxH) (inch)	23.62 x 6.46 x 16.18
	Weight (Net kg)	4.1
	Weight (Gross kg)	5.6
Weight	Weight Without Stand (kg)	3
Warranty	Warranty	24M