

Vacuum Cleaner LXT®

DCL184Z

18V • 54 mbar • 0.5 l

Excellent vacuum cleaner for cleaning car interiors and other compact areas

Battery-powered vacuum cleaner specially designed for cleaning car interiors. Four different types of nozzles ideal for vacuuming a car. Convenient blowing function to, for example, dry the car prior to waxing. Operating time 20 minutes with 18V LXT 3.0Ah battery.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery protection	✓
Air volume	1,4 m³/min
Max. sealed suction	54 mbar
Continuous Use 18V / 3.0 Ah Battery	80 / 30 / 20 min
Tank Capacity for Dust	0,5 L
Dust Bag Capacity	0,33 L
Vibration Level (3 axes)	≤ 0,4 m/s²
Tool weight with battery (EPTA)	1,8 - 2,2 kg
Product Dimensions (L x W x H):	365 x 138 x 202 mm
Shoulder Belt	✓

User benefits

- Low noise level for pleasant work.
- Adjustable suction power.
- Battery protection circuit protects against overloading, over-discharging and over-heating

EAN 0088381725910

Link to product - www.makitauk.com



Related products

Standard AC

459056-4

Floor Mat Nozzle 120 x 28mm



194566-1

Paper filter Anti-bacterial type, 5 pcs



140H94-2

Soft Brush 360 Complete Set, Blue



422437-5

Rubber Crevice Nozzel 330 x Ø35



140H95-0

Seat Nozzel, Ø32 Mm



140J64-3

Blower Nozzle Set



162544-9

Shoulder Belt, CI121D



Optional AC

123486-2

Floor T-Nozzle 225 mm, White



123488-8

Floor T-Nozzle 225 mm, Blue



123539-7

Floor T-Nozzle 225 mm, Black



140H94-2

Soft Brush 360 Complete Set, Blue



140H95-0

Seat Nozzel, Ø32 Mm



162544-9

Shoulder Belt, CI121D



166084-9

Cloth Dust Bag



191D67-4

Round brush



191D79-7

Straight Pipe



191D80-2

Straight Pipe 320 mm



191G86-8

Nozzle assembly set



194566-1

Paper filter Anti-bacterial type, 5 pcs



198523-1

T nozzle Ø28 mm



198525-7

T nozzle



198532-0

Nozzle assembly 320 mm



198538-8

Shelf Brush Nozzle 180 x 28 / 32 mm,



198559-0

Telescopic Pipe Ø28 x 500 - 850 mm



198745-3

Paper Filter set



198746-1

Cloth Dust Bag



198747-9

Dust Bag



198748-7

Easy shake off Dust bag set



198749-5

Easy shake off Dust bag set



198873-4

Shelf Brush White



198878-4

Round Brush 28 mm Tip, White



Optional AC

198919-6

Corner nozzle white

199038-1

Seat Nozzle Set 175 mm

199439-3

Crevice nozzle

422437-5

Rubber Crevice Nozzel 330 x Ø35

451241-5

Plastic Straight Pipe 28 x 465 mm,

451244-9

Plastic Straight Pipe 28 x 465 mm,

456587-4

Straight pipe Ø 28 mm, 465 mm

832188-6

Tool Bag



198990-0

Long sash nozzle set



199041-2

Seat nozzle set



416041-0

Sash Nozzle 160 x 30 mm



451240-7

Crevice nozzle short white



451243-1

Sash Nozzle, Blue



451424-7

Plastic Straight Pipe 28 x 465 mm,



459056-4

Floor Mat Nozzle 120 x 28mm



Other

User manual

Parts drawing