

Table Saw

2712

2 000 W • 315 mm

Efficient, high-accuracy table saw

An accurate table saw with a 2 000 W motor and speed of 3 400 min⁻¹ for professional use. A solid guide at the back and front. Max. sawing depth of 93 mm at a 90° angle and 64 mm at a 45° angle. Max. cutting width of 65 cm with the control. Saw is equipped with a table extension.



Technical specifications

Maximum Output Power	2000 W
No load speed	3400 min ⁻¹
Max. Cutting Height (above Table) at 45°	58 mm
Max. Bevel Range (Left)	45 / 0 °
Blade Diameter	315 x 30 mm
Power Supply Cord	3,0 m
Sound Power Level (L _{WA})	105 dB(A)
Sound Pressure Level (L _{pA})	93 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Weight Without Cable (EPTA-Procedure 01/2003)	52,9 kg
Product Dimensions (L x W x H):	1670 x 700 x 810 mm

User benefits

- Table saw with induction motor for quiet operation and low maintenance
- Precise adjustable rip fence
- Angle adjustment from 0 ° to 45 °
- Incl. Wheels and handles for easy transport

EAN 0088381673242

Link to product - www.makita.uk.com



Related products

■ Other

Parts drawing