



24" Traveller 12-Volt Smart TV with Freeview Play

- 24" HD Ready LED TV
- Official WebOS Hub Smart platform
- Download apps through the web browser
- Satellite tuner built-in with Freesat
- 3 x HDMI inputs for your external devices and consoles
- Wall mountable

	EAN	5060750402382
General features	Model number	CS24WS01
	Screen size	24"
	Max Resolution	1366 x 768
	HD Ready, Full HD	HD Ready
	Contrast Ratio	3000:1
	Brightness	180cd/m
	Display Colours	16.7M
	Viewing Angle	89/89/89/89 (CR>=10)
	Cabinet Colour	Black
	Wall mounting sizes	100 x 100mm (M4 x 8)
Reception	TV system	DVB-S, DVB-S2, DVB-T, DVB-T2, CI
	RF Antenna	Yes
Sound	Stereo system	Yes
	Audio output	2 x 3W
Inputs / outputs	RF Antenna	x1
	HDMI	x3
	CVBS	x1
	Audio in	N/A
	Digital Audio Out	x1
	Earphone Out	x1
	USB	x2
	CI	x1
	RJ45	x1

Other Features	DVD	No
	Smart	Yes
	Freeview Play	Yes
	Available Apps	Netflix, Disney +, Prime Video, Youtube, Catch Up TV apps
	OSD Language	English, French, German, Spanish, Portuguese, Italian
	EPG (Electronic Program Guide)	7 Days
	Sleep Timer	Yes

Power	Operation Power Consumption	21W
	Max Power Consumption	36W
	Power Supply	DC 12V 3A
	Standby power consumption	≤0.5W
	Energy Efficiency Class	F

In the box	Remote Control	Yes
	Power Cable	Yes
	Warranty	Yes
	Battery	AAA x 2
	12 volt cable	Yes

Dimensions	Unit with stand (W x D x H)	W 550 x H 369 x D 142 mm
	Unit without stand (W x D x H)	W 550 x H 325 x D 91 mm
	Weight (kg)	2.75kg