

# PowerCat 6A DataGate Shielded Straight and Side Entry Jack

The Category 6A DataGate Shielded Jack is a key component of the PowerCat 6A shielded end-to-end solution.

The PowerCat 6A DataGate jack offers superior alien crosstalk suppression, excellent insertion loss, and provides enhanced electromagnetic interference (EMI) protection by utilizing robust die cast zinc alloy jack body housing. This shielded jack also features a unique spring loaded shutter that not only protects it from dust and contaminates, but the ingenious spring loaded design also ejects improperly seated patch cords. The shielded jack is dual colour coded for either 568A or 568B wiring schedules. The Molex C6A DataGate RJ45 360 ° shielded jack accommodates flexible cable routing by allowing 90 ° or 180 ° cable entry.

The PowerCat 6A DataGate Shielded Jack was specifically designed for highspeed 10GB data transmission. This unique modular jack is also backwards compatible with Shielded C6 and C5e systems.

Molex recommends that the full range of PowerCat 6A Shielded products be used in an end-to-end system to maximize cabling performance. This system is compliant with the ISO/IEC 11801 Amd 1 and ANSI/TIA-568.2-D requirements for the support of 10GBASE-T transmission.







## **FEATURES & ADVANTAGES**

Robust die cast zinc alloy housing

360°Shielded

Accommodates flexible cable routing by allowing 90 ° or 180 ° cable entry

Dual Color coding allows 568A/B wiring

Patented IDC (insulation displacement contact) V-shaped contacts that flex not fatigue when terminated

Spring-Loaded Shutter

Accepts color coded port identification labels

Category 6A performance when installed as a complete PowerCat Shielded System

Spring loaded cable/drain wire clamp

Cable can be terminated in 3 directions - Straight, on left or right side of jack

Complies with ISO/IEC 11801 and TIA Cat 6A channel and PL requirements

Jack can be terminated with 4 Pair Termination Tool or standard IDC Punch Down Tool

**RoHS Compliant** 

Molex DataGate jacks may accommodate both solid (AWG22 to AWG24) and stranded (AWG26) cables

www.molexces.com/products/copper/cat6a/



# PowerCat 6A DataGate Shielded Straight and Side Entry Jack

## **SPECIFICATIONS**

### **Commercial**

ANSI/TIA-568.2-D-2018 ISO 11801:2017 IEC 60603-7 UL 1863 CSA C22.2

### **Mechanical**

**RI45 Connector** 

Connector Housing: Zinc Alloy plated bright

Ni/Cu

**Operating Life:** Minimum 750 insertion

cycles

**Contact Material:** Copper Alloy

**Contact Plating:** 50μ Gold/ 50μ Nickel

minimum

Contact Force: 100g minimum
Plug Retention Force: 6.8kg minimum

**IDC Connector** 

**Housing:** Thermoplastic, UL94V-0

**Operating Life:** Minimum 20

reterminations

Contact Material: Copper Alloy IDC Contact Plating: Matte Tin Contact Force: 100g minimum

Wire Accommodation: 22-24 AWG solid and

26 AWG stranded

### **Electrical**

Interface Resistance:  $20m\Omega$ Initial Contact Resistance:  $2.5m\Omega$ Insulation Resistance:  $>100M\Omega$ 

### **Physical**

**Minimum Backbox Depth Requirement:** 

refer table

Shipping Weight: 25g (0.88 oz)

**Dimensions:** 17.8mm(W) x 23.1mm(H)

x 41.3mm(L)

Country	Minimum Backbox Depth	
Australia and New Zealand	44 mm	
China	44 mm	
Europe, Middle East and Africa Wall Outlet Bezel/Module Styles:		
Euromod II 25 x 50mm 32 mm		
Mod-Snap III 25mm x 38.5 44 mm		
Contura 22 x 50mm 44 mm		
Legrand ® Compatible 22.5 x 45mm 44 mm		
DIN 49075 50 x 50mm	44 mm	
India	50 mm	
Russia 85 mm		
USA	3.35 in	

www.molexces.com/products/copper/cat6a/



# PowerCat 6A DataGate Shielded Straight and Side Entry Jack

# **ORDERING INFORMATION**

Order No.	SAP No.	Description
KSJ-00096-01	183010132	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-ALMOND
KSJ-00096-02	183010133	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-WHITE
KSJ-00096-04	183010134	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-BLACK
KSJ-00096-BL	183010135	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-BLUE
KSJ-00096-08	183010136	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-GRAY
KSJ-00096-GR	183010137	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-GREEN
KSJ-00096-05	183010138	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-IVORY
KSJ-00096-RG	183010139	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-ORANGE
KSJ-00096-PP	183010140	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-PURPLE
KSJ-00096-RD	183010141	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-RED
KSJ-00096-YL	183010142	JACK DATA GATE CAT6A SHIELDED 568A/B UNIVERSAL SHUTTER-YELLOW
Termination Tool		
31.0011	182520002	4 Pair Termination Tool Frame
31.0015	182520015	4 Pair Termination Lacing Head C6A
31-001	18030001	110 Punchdown Termination Tool