

Heated Jacket LXT®

DCJ205ZO

14,4V / 18V • Olive

Heated jacket with five heating elements and three heat settings

A heated jacket with a 14.4V or 18V LXT battery for harsh conditions. The jacket's water-repellent material protects against light rain. Two heating elements on the front, three on the back. The run time with a 5.0Ah battery is 8 / 16 / 28 h, depending on heating level. Batteries and charger are sold separately.



Technical specifications

Battery protection	✓
Voltage LXT	✓
Nominal Battery Voltage	14,4 V / 18 V
Continuous Use 18V / 3.0 Ah Battery	4 / 6 / 17 h
Tool weight with battery (EPTA)	1,1 - 1,2 kg

User benefits

- 5 Heat zones (left chest, right chest, back upper left, back upper right, back centre)
- Switch for 3 heat level settings with LED indicator change in blue, white, red
- Running time with 18V 6Ah battery: 8.5 / 14 / 35 hours (high/medium/low).
- Battery pocket on back left. Battery can be fixed at waist with the belt clip of Battery holder.

Link to product - www.makita.uk.com



Related products