

HU362AWCVW

Safety switch, heavy duty, non fusible, 60A,
600 VAC/VDC, 3 poles, 60 hp, NEMA 12K,
crouse hinds arktime, viewing window



Main

Product	Receptacle Switch
For Use With	Plug APJ6485 Crouse-Hinds Arktime
Disconnect Type	Non-fusible disconnect
Phase	3 phase
Number of Poles	3
Current rating	60 A
Voltage Rating	600 V AC 250 V DC
Enclosure Rating NEMA 3R	NEMA 12K
Maximum Horse Power Rating	50 Hp at 480 V AC 50-60 Hz for 3 phase motors 60 Hp at 600 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC

Complementary

Mounting Type	Surface
Electrical Connection	Receptacle
Wire Configuration	Without neutral 4-wire
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening torque	45 Lbf.in (5.08 N.m) (AWG 6...AWG 4) 40 Lbf.in (4.52 N.m) (AWG 8) 35 lbf.in (3.95 N.m) (AWG 14...AWG 10)
Depth	7 in (177.80 mm)
Width	10.5 in (266.70 mm)
Height	16.5 in (419.10 mm)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00118-H&HU SW,W/C-HINDS RECPT-WC
Discount Schedule	DE1
GTIN	785901208990
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.75 in (47.625 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	10.37 in (26.352 cm)
Package 1 Weight	10.00 lb(US) (4.536 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------