

H361NRB

Safety switch, heavy duty, fusible, 30A, 4 wire,
3 poles, 1 neutral, 20hp, 600VAC/DC, Type 3R,
bolt on hub provision



Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number of Poles	3
Current Rating	30 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R galvanized steel
Motor power hp	5 Hp at 480 V AC 50-60 Hz for 3 phase motors 15 Hp at 480 V AC 50-60 Hz for 3 phase motors 7.5 Hp at 600 V AC 50-60 Hz for 3 phase motors 20 Hp at 600 V AC 50-60 Hz for 3 phase motors 15 hp at 600 V DC

Complementary

Fuse type	H or K R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	4-wire (3PH + N)
Wire Size	AWG 12...AWG 6 aluminium AWG 14...AWG 6 copper
Tightening torque	45 Lbf.in (5.08 N.m) 0.02 in ² (13.3 mm ²) (AWG 6) 40 Lbf.in (4.52 N.m) 0.01 in ² (8.367 mm ²) (AWG 8) 35 lbf.in (3.95 N.m) 0.00...0.01 in ² (2.06...5.261 mm ²) (AWG 14...AWG 10)
Depth	4.86 in (123.44 mm)
Width	7.55 in (191.77 mm)
Height	14.88 in (377.95 mm)
Net Weight	8.82 lb(US) (4 kg)

Environment

Certifications	UL listed file E2875
----------------	----------------------

Ordering and shipping details

Category	00009-H&HU SW,2&3P,N3R,30-200A
Discount Schedule	DE1
GTIN	785901122487
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.20 in (13.208 cm)
Package 1 Width	7.70 in (19.558 cm)
Package 1 Length	16.20 in (41.148 cm)
Package 1 Weight	8.77 lb(US) (3.978 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	120
Package 2 Height	45.50 in (115.57 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1086.00 lb(US) (492.601 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------