

Product data sheet

Characteristics

8702SEO1V07

NEMA Contactor, Type S, reversing, vertical,
Size 3, 90A, 50 HP at 575 VAC, 3 phase, 3
pole, 600 VAC coil, open style



Main

Product Type	Contactors
Product Range	Type S
Contactors Type	Reversing

Complementary

NEMA Size	3
Rated Current	90 A
Number of Poles	3P
Mounting Orientation	Vertical
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	25 HP 200 V AC 30 HP 230 V AC 50 HP 460 V AC 50 HP 575 V AC
Coil Voltage	550 V AC 50 Hz 600 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	19.02 in (483 mm)
Width	7.20 in (183 mm)
Depth	7.01 in (178 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	CSA UL Listed


Ordering and shipping details

Category	21273-8702,36 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	3606482141063
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.02 in (48.3 cm)
Package 1 Width	7.20 in (18.3 cm)
Package 1 Length	7.01 in (17.8 cm)
Package 1 Weight	27.67 lb(US) (12.55 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------