

Product data sheet

Characteristics

8903SMO2V02

Contactor, Type S, multipole lighting,
electrically held, 30A, 3 pole, 110/120 VAC
50/60 Hz coil, open style



Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	3.50 in (89 mm)
Depth	4.21 in (107 mm)
Width	3.23 in (82 mm)

Environment

Enclosure Type	Not rated (open device) surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21325-8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
GTIN	785901619529
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.61 in (11.7 cm)
Package 1 Width	5.91 in (15.0 cm)
Package 1 Length	8.11 in (20.6 cm)
Package 1 Weight	3.13 lb(US) (1.42 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------