

CH362DSWC

Safety switch, heavy duty, fusible, 60A, 600 VAC/VDC, 3 poles, 50 hp, NEMA 4, 4X, 5, 304 steel, crouse hinds



Main

Range	Square D
Product	Receptacle Switch
For Use With	Wiring connection APJ6485 Crouse-Hinds Arktite
Current Rating	60 A
Enclosure Rating	NEMA 3/3R/4/4X/5/12 stainless steel 304
Horsepower Rating	15 Hp at 480 V AC 50-60 Hz for 3 phase motors 30 Hp at 480 V AC 50-60 Hz for 3 phase motors 15 Hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 3 phase motors
Disconnect Type	Fusible disconnect
Short Circuit Current Rating	200 KA 10 kA
Mounting Type	Surface
Number of Poles	3
Phase	3 phase
Electrical Connection	Receptacle
Certifications	CSA
Voltage Rating	600 V AC/DC
Wire Configuration	4-wire
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper

Complementary

Tightening torque	50 Lbf.In (5.65 N.m) (AWG 3) 45 Lbf.In (5.08 N.m) (AWG 6...AWG 4) 40 Lbf.In (4.52 N.m) (AWG 8) 50 lbf.in (5.65 N.m) 0.00...0.01 in ² (2.06...5.21 mm ²) (AWG 14...AWG 10)
Width	10.79 in (274.07 mm)
Height	16.87 in (428.50 mm)
Depth	5.11 in (129.79 mm)

Ordering and shipping details

Category	00153-C,CH&CHU CANADA SW NON-NEG
Discount Schedule	DE1
GTIN	785901344490
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.70 in (19.558 cm)
Package 1 Width	13.80 in (35.052 cm)
Package 1 Length	32.50 in (82.55 cm)
Package 1 Weight	28.83 lb(US) (13.077 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes