

# **TECHNICAL SPECIFICATION**

**MODEL NO : A-1398**

**Bluetooth Audio Transceiver**

## **Features & SPECIFICATIONS**

- **Bluetooth devices searching automatically to realize connect, transmit wireless audio transmission**
- **No APP and driver need.**
- **Noise reduction and echo cancellation**
- **Multi-band equalizer configuration**
- **Support voice prompts**
- **Integrated Li-Type battery charger and support 300 mA fast charge and over-discharge protection**
- **Built-AEC echo cancellation and noise cancellation circuit ANC**
- **Built-in enhanced signal transmission circuit, connected faster and more stable**
- **Automatic memory connected function , the operation is easier, more convenient**

Bluetooth Version	Bluetooth 5.0、Consume low power (A2DP)	
Supported protocol	A2DP, AVRCP, HFP, SPP HID	
Current Consumption	≤ 43MA (Receiving Mode)	
	≤ 60MA (Transmitting Mode)	
	< 18MA (Standby Mode)	
Built-in battery	Polymer 300MAH	
Charging current and time	2 Hours, 300MA	
Playing Period	8Hours	
Bluetooth distance	10M	
Interface	Micro USB (For Charging)	
	3.5MM stereo jack (For Transmitting and Receiving)	
Compatibility	All Bluetooth audio devices. (smartphone/PC/ Notebook/Bluetooth phone., etc)	

**TEN-TRONICS CO., LTD.**

**ADDRESS : NO.33.LANE 347,CHUNG-SAN S.ROAD**

**YOUNG-KANG DIST,TAINAN CITY,TAIWAN,R.O.C.**

**TEL : 886-6-2310285 (REP.)      FAX : 886-6-2016087**

**天 子 電 子 股 份 有 限 公 司**

**廠址：台南市永康區中山南路347巷33號**

**電話：(06)2310285 (代表號)    傳真：(06)2016087**