# K3-RGB


**USER MANUAL** 





# **INSTALLATION**

Connect the K3 to the USB port. Driver installation starts automatically.



### **SETTINGS AND FUNCTIONS**

The K3 features a range of customization options and convenient quick keys. All settings are made directly on the keyboard, by pressing the FN key + the desired setting key.

### **RGB LED ILLUMINATION**



Press FN + INS to start a cycle of shifting backlight colors.



Press FN + HOME repeatedly to switch between 7 different background colors.



Press FN + PGUP for LED illumination in 6 color zones. To set the color of each zone, press FN+ PGUP again. When the NUM, CAPS and SCROLL lights in the upper right corner blink, press FN + the numbers 1–6 repeatedly to adjust the colors. When you're done, press FN+PGUP again.



Press FN + DEL repeatedly to switch between two different wave effects.



Press FN + END once to start the 7-color breathing effect cycle, and twice to lock the breathing effect at the current color.



Press FN + PGDN to start a multi-color typing effect. (Visible when typing.)



Press FN + the up/down arrow keys to increase/decrease the brightness of the LED lighting.



Press FN + the left/right arrow keys to decrease/increase the speed of the LED effects.

# OTHER USEFUL KEYS AND SHORTCUTS

FN + **y** = Lock Windows key

FN + F1-F8 = Media controls

FN + F9 = E-mail

FN + F10 = Web browser

FN + F11 = Lock all keys

FN + F12 = Calculator



# **TROUBLESHOOTING**

Make sure the K3's USB connector is firmly attached to your computer's USB port.

Connect to another USB port.

Connect to another computer.

### **TECHNICAL SPECIFICATIONS**

Model name: XG-K3-RGB

Available layouts: Nordic, UK, US, German, French, Spanish, Belgian, Estonian, Portuguese, Swiss

Illumination: RGB LED lighting

Keys: Standard 105

Key cap layout: Step Scalpture2 Type

Anti-Ghosting: 19-key rollover Key switches: Mem-chanical

Special keys/shortcuts: Illumination settings, Media controls

Connection: USB Weight: 1,1 kg

Size: 137 x 444 x 43 mm Cable: 1.8 m, braided

Warranty EU/US/ASIA: 2/1/1 years

## **CHECK OUT MORE XTRFY PRODUCTS AT XTRFY.COM**

