

UIC558-13PIN-MI-CRT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 013 3001
Specification	UIC558-13PIN-MI-CRT
HARTING eCatalogue	https://b2b.harting.com/09580133001

Identification

Category	Inserts
Series	HARTING UIC 558

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	13
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	>10 ⁷ Ω
Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 550
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	35 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140186965
eCI@ss	27440205 Contact insert for industrial connectors