

Human Machine Interface Touch Screen

multicomp PRO

**RoHS
Compliant**



Specifications

Model		MP011740	MP011741	MP011742
Item		Specifications		
CPU		Cortex A35 1.2GHz		
Touch Screen		Resistive		
Display	Screen Size	7 Inch	10.2 Inch	15 Inch
	Resolution	800 × 480	1024 × 600	1920 × 1080
	Brightness	250 cd/m ²	350 cd/m ²	250 cd/m ²
	Backlight Type	LED		
	Backlight Life	50,000 Hours		
	Colors	16,000k colors		2,60k colors.
Storage	Flash	128 MB		46GB
	RAM	DDRIII 128MB		DDRII 512MB
	SD Card	YES		YES (TF card)
I/O Port	USB	USB Host: USB2.0 x1; USB Client: USB 2.0 x1 (cannot be used at the same time)		
	Serial Port	Type 1: COM1 (RS232), COM1 (RS485), COM1 (RS485)		
		Type 2: COM1 (RS232), COM1 (RS422), COM1 (RS485)		
	Ethernet	YES		
	CAN	N/A		
4G/WIFI Module	Optional			
Permanent Calendar		Built-in		
Power	Power Supply	24V DC (12~28V DC)		24V DC (18~28V DC)
	Power Consumption	<8W	<10W	<15W
Dimension	Enclosure	Plastic+ABS (Polycarbonate)		Aluminum + Metal + ABS
	Dimension{mm}	201.2W × 147.2H×38D0	272W × 191H×41.6D	403W × 253.0H×35.2D
	Mounting Size(mm)	192W × 138H	260W × 179H	384W × 244H
	Net Weight (KG)	0.52	1.02	248

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Human Machine Interface Touch Screen

multicomp PRO

Model		MP011740	MP011741	MP011742
Environment	Protection	1P65 (Front panel)		
	Temperature	Storage: -20C~70C		Storage: -20C~60T
		Working: -10C~65C		Working: 0C~50C
	Humidity	10 ~90%RH (Non-condensing)		
Vibration Resistance	10 ~ 28 Hz (X,Y, Z direction 2G/30 minutes)			
CE Certification		CE Marked		
FCC Certification		FCC Class A		
Programming Software		PI Studio		
Software	IoT Service (optional)	Real-time Monitoring Points: 100		Real-time Monitoring Points: 300
		Alarm Monitoring Points: 20		Alarm Monitoring Points: 200
		History Monitoring Points: 50		History Monitoring Points: 100
		History Storage: 60 days / 1 millions		History Storags: 120 days / 1 millions
	VPN Pass-through	YES		

Part Number Table

Description	Part Number
HMI-Touch Screen, 800 × 480, 7"	MP011740
HMI-Touch Screen, 1024 × 600, 10.2"	MP011741
HMI-Touch Screen, 1920 × 1080, 15"	MP011742

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO