



## PUMA 30W / 100V METAL HORN LOUDSPEAKER

The Puma 30 is an economically priced, round, metal horn loudspeakers. With a response more suitable for speech, these horns are designed for internal or external use, having an IP66 rating. They are ideal for excellent sound distribution for a wide range of outdoor applications including car parks, factories and warehouses, security areas, events venues and other indoor and outdoor areas. These speakers are for 100 volt line Public Address applications, and each has a range of power tapings. The horns come supplied with a swivel bracket.

The different horns available are the Puma 10 (10 watt rms output), Puma 15 (15 watt output) and Puma 30 (30 watt output).

- .30 watt rms, 100 volt line, rectangular, ABS horn loudspeaker.
- .30 watt, 15 watt, 10 watt, 5 watt, 3 watt and 1 watt power tapings.
- .IP66 rating for external use.
- .Supplied with swivel bracket.

## TECHNICAL SPECIFICATIONS

|                            |                      |
|----------------------------|----------------------|
| <b>Order Code:</b>         | 04-0006-B10          |
| <b>Model:</b>              | Puma 30              |
| <b>Power Taps:</b>         | 30, 15, 10, 5, 3, 1W |
| <b>Frequency Response:</b> | 250Hz - 16kHz        |
| <b>Sensitivity:</b>        | 109dB(A) at 1W/1m    |
| <b>IP Rating:</b>          | IP66                 |
| <b>Colour:</b>             | Grey                 |
| <b>Material:</b>           | Metal horn           |
| <b>Dimensions:</b>         | 266diameter x 263mm  |
| <b>Weight:</b>             | 2.10kg               |