

ABS M 95 G



Sample image

Order symbol : ABS M 95 G

Product nr : 8784318

Description : Enclosure, ABS


Remarks : Grey cover

EAN : 6418074002334

El. number :

- Finland : 3423469
- Denmark : 8212002076
- Sweden : 2536729

Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and polyamide cover screws.



Dimensions :

	Height	Width	Depth
mm :	230	140	95
inch :	9.06	5.51	3.74

Materials :

Material :	ABS
Base colour :	RAL 7035 -light grey
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Accessories :

CHM-3	DIN-35 Mounting rail, for enclosures: (110 x 35 x 1)
FM-3	DIN-35 Mounting rail, for enclosures: (35 x 200 x 1)
FP 22046	Wall fastening lug (4 pcs)
M-MP	Mounting plate, for enclosures: (185 x 94 x 1)

Ratings :

Ingress protection (EN 60529):	IP66; IP67;
--------------------------------	-------------

Temperatures :

Temperature °C (short term) :	-40 ... 80
Temperature °F (short term) :	-40 ... 175
Temperature °F (continuous) :	-40 ... 140

Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C :	650C

Certificates :

SGSFIMKO_PICC_pc