

# USB Panel Mount Chargers

## 3 OPTIONS

- Input voltage 12vdc - 24vdc
- 3 models to choose from
- Aluminium finish
- Integrated On Off Switch
- All versions supplied complete with 10A fuse cable

### Option 1. Part number USB-C-PANEL-B-DUAL



- Dual 45W USB C ports
- Features PD power delivery
- Ultra Fast Charging
- Fireproof ABS
- 90W max. load
- 12 - 24V input
- Supplied with 60cm connecting cable
- (10A fuse supplied)
- on / off button
- Protective Cover



### Option 2. Part number USB-C-PANEL-B



- USB A port 18W QC3.0 + USB C port PD 30W
- Fireproof ABS
- 48W max. load
- 12 - 24V input
- Supplied with 60cm connecting cable (10A fuse)
- On / off button
- Protective cover

### Option 3. Part number USB-C-PANEL-CHG



- USB A port 18W QC3.0 + 2 x USB C port PD 45W
- Fireproof ABS
- 108W max. load
- 12 - 24V input
- Supplied with 60cm connecting cable (10A fuse)
- On / off button
- Protective Cover

## TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.