

# Part Number: P-R2-K3RF3-M2

Panel Interface Connector with Category 5e RJ45; Panel Mount Housing and Metal Cover; GFCI Inside-Outlet 125 VAC Outlet, 3A Circuit Breaker

<https://shop.graceport.com/products/p-r2-k3rf3-m2>



## Product Specifications

### Description Detail

Panel Interface Connector that typically mounts to the outside of a control panel housing. These programming ports eliminate the need to open the panel door and improve safety and compliance to NFPA 70e. We offer 15,000+ combinations of components and outlets.

### Component Details

Component Code	R2
Component Quantity	1
Component Description	Category 5e RJ45
Component Type	Bulkhead
Gender Front	RJ45 Female
Gender Back	RJ45 Female

### Electrical Specifications

Power Type	Domestic GFCI Inside-Outside Rear Outlet
Power VAC	125
Power AMPs	15
Circuit Breaker	3A
SCCR Rating	0.2kA


**Mechanical Specifications**

Enclosure Rating	IP65
Housing Size	K Size Housing
UL Type	Type 4
Latch	Type 304 Stainless Steel
Cover	Polycarbonate, UV rated

**Commercial Data**

Country of Origin	US
Schedule B Code	8537.10.9090

**Datasheets**

Name	
GracePort Datasheet	

**Don't see what you're looking for?**

Contact us at [sales@gracetechnologies.com](mailto:sales@gracetechnologies.com), call 1-800-280-9517 or visit [www.graceport.com](http://www.graceport.com) to chat with our customer service.