

12V 300mA Power Supply

Universal compact power supply for masthead amplifiers

Features

- Ultra compact
- Low noise mains powered unit
- 12V=300mA output, suitable for powering most masthead amplifiers
- F connector sockets for secure connections



Product Specifications

Outputs	12VDC +/-5% 300mA
Insertion Loss	0.5dB (87-790MHz)
Signal Frequency Range:	5...1000MHz
Maximum Power Consumption	220-240V ~ 50/60Hz <3.6W
No Load Power Consumption	220-240V ~ 50/60Hz <0.07W
Connectors	F-type (female) IEC60169-24
Operating Temperature	0...40°C
Power indicator:	Green LED

Product Information

EAN	5050171073322
Unit Quantity	1
Unit Dimensions	8 x 9.1 x 5.2cm
Unit Weight	178g
Outer Quantity	48
Outer Dimensions	51.5 x 23 x 24cm
Outer Gross Weight	9.28kg
Outer Net Weight	8.83kg