

PERFORMANCE

Processor

MediaTek Helio G80 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)

Graphics

Integrated ARM Mali-G52 MC2 GPU

Chipset

MediaTek SoC Platform

Memory

3GB Soldered LPDDR4x

Storage

32GB eMMC 5.1

Expandable Memory

microSD Card (up to 128GB, FAT32; 2TB, exFAT)

Card Reader

microSD Card Slot

Storage Support

- 32GB eMMC 5.1 on systemboard
- microSD card, supports FAT32 up to 128GB, exFAT up to 2TB

Speakers

Dual speaker optimized with Dolby® Atmos®

Microphone

Mono

Camera

Front 2.0MP / Rear 8.0MP

VoiceCall

No

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Coulomb counter
- Hall sensor

Vibration Motor

Eccentric Rotating Mass (ERM)

Battery

Integrated 5100mAh (Typ.)

Max Battery Life

Video playback: 13 hr

Web browsing: 12 hr

Music playback: 15 hr

Power Adapter

5V / 2A

DESIGN

Display

9" HD (1340x800) IPS 400nits Anti-fingerprint, Touch

Touchscreen

In-cell, 10-point Multi-touch

Case Material

Metal (Back Cover)

Keyboard

None

Pen

No Support

Dimensions (WxDxH)

215.43 x 136.76 x 7.99 mm (8.48 x 5.38 x 0.31 inches)

Weight

Around 344 g (0.76 lbs)

Case Color

Arctic Grey

SOFTWARE

Operating System

Android™ 12 or Later

CONNECTIVITY

WLAN + Bluetooth®

11ac 1x1 + BT5.1

WWAN

None

NFC

None

Location Services

GPS + GLONASS + Galileo

Standard Ports

- 1x USB-C® 2.0 (support data transfer, charging, USB-C digital headset)
- 1x Card slot
- 1x 3.5mm headphone jack

Docking

None

SECURITY & PRIVACY

MANAGEABILITY

SERVICE

Base Warranty

1-year, Courier with 1-year Battery

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

Product : TB310FU

TopSeller : Yes

Announce Date : 2023-01-31

EAN / UPC / JAN : 196802847575



Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference