

Product Specification



Model
LG 50UR78006LK



Energy consumption

Energy efficiency class (SDR) F
On mode power demand (SDR) 64.8 W
Energy efficiency class (HDR) G
On mode power demand (HDR) 99 W

Audio

Audio power 20 W
Sound technology AI Sound (Virtual 5.1 Up-mix)
Speakers 2

Connectivity

Audio output Optical x 1

Connections

- HDMI 2.0 X 3 (eARC compatible)
- USB 2.0 x 2
WiFi Built-in WiFi
Ethernet Yes
Bluetooth Bluetooth 5.0

Screen

Screen technology LED directlit
Resolution 4K Ultra HD 3840 x 2160p
Screen size 50"
HDR - HDR10 - Hybrid Log Gamma (HLG)
HDR technology Active HDR

Features

Table-top stand Yes
VESA mount 200 x 200
Other features - Sleep timer - Parental lock
PVR function Yes

Weight

- TV with stand: 11.8 kg
- TV: 11.7 kg
- Boxed: 14.5 kg

Dimensions

- TV with stand: 716 x 1121 x 230 mm (H x W x D)
- TV: 651 x 1121 x 57.1 mm (H x W x D)
- Boxed: 775 x 1215 x 152 mm (H x W x D)

Colour

- TV: Dark iron grey
- Stand: Light black

Box contents

- LG 50UR78006LK 50" Smart 4K Ultra HD HDR LED TV
- Standard remote
- TV stand
- Batteries
- Screws
- Manual