



3E3KS-230-MAIN




3E0600-EPE

Overview

- IP54 Euro-profile keyswitch
- 3 Position
- Maintained contact
- Heavy duty all metal construction
- External / Internal applications
- Key to differ as standard, Key Alike option
- Suitable for roller shutter applications
- Surface mount c/w back box 75 mm x 75 mm x 45 mm
- Complete with cylinder and three keys
- Optional hinged cylinder cover (IP65)

Dimensions (mm) :



- 3 Position
- Maintained Contact
- Key To Differ As Standard
- Surface Mount
- c/w Cylinder and Three Keys

IMPORTANT: This product is for use in 12Vdc and 24Vdc applications only and should only be installed by a qualified person

Technical (Cylinder)

Finish	Polished Nickel
Pins	6
Keys	3
Escutcheon	Hinged Cover, IP65 (optional)

Technical (Electrical)

Switch Rating	230V ac, 16amps
Ingress Protection	IP54

Specification: (panel)

Material	Aluminium
----------	-----------

Ordering information:

3E3KS-230-MAIN 3 Position Maintained Euro profile keyswitch 230v c/w cylinder

3E0600-EPE Euro-profile Escutcheon – Hinged Cover IP65