

Technical Specification

Product Code: VPSC125WH

Description: Single Telephone Outlet (Secondary)



General Information

Plate Dimensions (mm)	88 (W) x 88 (H) x 8 (D)	
Dimensions With Gasket (mm)	91 (W) x 91 (H) x 9 (D)	
Plate Fixing Centres - Horizontal (mm)	60.3	
Style	Victorian	
Finish	Satin Chrome	
Insert Colour	White	
Gasket Colour	White	
Materials	Front Plate: Stainless Steel	Insert: Urea
	Rear Housing: Polycarbonate	Terminals: Brass
	Earth Plate: Mild Steel	Gasket: Nylon
Anti Microbial Certified	No	
Termination Type	IDC	
Shielded	No	
Minimum Back Box Depth (mm)	16	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	

Additional Information For cleaning / polishing of products, use only a soft, dry, clean cloth.

