

Technical Specification

Product Code: VPSC157WH

Description: Isolated Satellite & Isolated Coaxial Outlet



General Information

Plate Dimensions (mm)	88 (W) x 88 (H) x 8 (D)	
Dimensions With Gasket (mm)	91 (W) x 91 (H) x 9 (D)	
Plate Fixing Centres - Horizontal (mm)	60.3	
Style	Victorian	
Finish	Satin Chrome	
Insert Colour	White	
Gasket Colour	White	
Materials	Front Plate: Stainless Steel	Insert: Urea
	Terminals: Brass	Earth Plate: Mild Steel
	Gasket: Nylon	
Anti Microbial Certified	No	
Termination Type	Screw	
Isolated	Yes	
Isolated Comments	Enables 1 way signal, reducing signal interference	
Non-Isolated	No	
Shielded	No	
Minimum Back Box Depth (mm)	16	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	Warranty - Electronics (Years) 1

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
 Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
 Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.
 Isolated socket will filter out any interference, if a 2 way signal is required, i.e. for use with satellite hard wire extensions, then a non-isolated outlet is required.

