

Technical Specification

Product Code: VPSC753WH

Description: 13A Ingot Fused Connection Unit With Neon



General Information

Plate Dimensions (mm)	88 (W) x 88 (H) x 8 (D)	
Dimensions With Gasket (mm)	91 (W) x 91 (H) x 9 (D)	
Plate Fixing Centres - Horizontal (mm)	60.3	
Style	Victorian	
Finish	Satin Chrome	
Insert Colour	White	
Gasket Colour	White	
Materials	Front Plate: Stainless Steel Fuse Drawer Cover: Stainless Steel Terminals: Brass Internal Busbars: Formed Pressed Brass Gasket: Nylon	Insert & Housing: Urea Neon Lens: Polycarbonate Terminal Screws: Steel & Yellow Passivated Earth Strap: Mild Steel
Anti Microbial Certified	No	
Rated Voltage (V~) (Ue)	250	Frequency (Hz) 50
Resistive Load Rating (A)	13	
Fuse Fitted Rating & Type	13A (BS 1362)	
Termination Type	Screw	
Terminal Size (mm)	Ø5	Terminal Torque Value (Nm) 2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4	
Switched	No	
Twin Earth Terminals	Yes	
Neon Indicator	Yes	Indicator Colour Red
Product Marking	Fused	
Minimum Back Box Depth (mm)	25	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	
Standards	BS 1363-4 BS 1362	

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.