

PRODUCT-DETAILS

Sentry SSR10MP

Sentry SSR10MP Safety relay



General Information

Extended Product Type	Sentry SSR10MP
Product ID	2TLA010050R0101
EAN	7350024486261
Catalog Description	Sentry SSR10MP Safety relay
Long Description	<p>Sentry SSR10MP Safety relay with relay outputs 3NO+1NC, 85-265 VAC/120-375 VDC supply voltage and push-in spring terminals. For monitoring of safety devices with contacts, 2 equivalent channels. Manual or automatic reset selectable by switch on front.</p> <p>Sentry safety relays cover various types of safety applications up to PLe / SIL3. Basic models provide reliable supervision of simpler safety functions, while universal models provide advanced features and high flexibility. Models with display offer preset configurations and extensive information to further simplify troubleshooting. Additional variants offer a high accuracy timer function of $\pm 1\%$ and an adjustable time setting range from 0-999 s.</p> <p>High output current capacity of up to 6 A can save the use of an intermediary contactor. Multi-reset allows up to 10 safety relays connected to one reset light-button.</p> <p>All models are available with detachable push-in or screw terminals. Terminals and coding kit to mark removed terminals are available as accessories.</p>

Ordering

EAN	7350024486261
Minimum Order Quantity	1 piece

Customs Tariff Number	85364900
-----------------------	----------

Popular Downloads

Data Sheet, Technical Information	2TLC010037L0201
Instructions and Manuals	2TLC010064M0201
CAD Dimensional Drawing	2CDC001079B0201
Dimension Diagram	2TLC010001U0201
Wiring Diagram	2TLC010008T0001
Marketing Video	2TLC010019N0201 2TLC010018N0201

Dimensions

Product Net Width	22.5 mm
Product Net Height	120 mm
Product Net Depth / Length	120 mm
Product Net Weight	0.214 kg

Technical

Function	Safety relay for monitoring of safety devices
Sub-Function	Start/test input, Manual/Auto reset selectable by switch
Timer Relay Type	No Time Delay
Rated Control Supply Voltage (U _s)	120 ... 375 V DC 85 ... 265 V AC
Degree of Protection	IP20
Connecting Capacity	Crimped Pin 1x0.2...2.5 mm ² Crimped Pin 2x0.25...1.5 mm ² Flexible with Ferrule 1x0.2...2.5 mm ² Flexible with Ferrule 2x0.25...1.5 mm ² Solid 1x0.2...2.5 mm ² Solid 2x0.25...1.5 mm ²
Wire Stripping Length	6.5 mm
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Standards	ISO 13849

Technical UL/CSA

Connecting Capacity UL/CSA	Crimped Pin 1x 24-14 AWG Flexible with Ferrule 1x 24-14 AWG Solid 1x 24-14 AWG
----------------------------	--

Environmental

Ambient Air Temperature	Operation -25 ... +65 °C Storage -40 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations

CQC Certificate	CQC2017010303977544
cUL Certificate	2TLC010006D0201
Declaration of Conformity - CCC	2020980303000244
Declaration of Conformity - CE	2TLC010010D0201
Declaration of Conformity - UKCA	2TLC010190D0201
TÜV Certificate	2TLC010008D0201

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	125 mm
Package Level 1 Depth / Length	31 mm
Package Level 1 Height	129 mm
Package Level 1 Gross Weight	0.275 kg
Package Level 1 EAN	7350024486261
Package Level 2 Units	36 piece
Package Level 2 Width	280 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Height	210 mm
Package Level 2 Gross Weight	10.2 kg

Classifications

Object Classification Code	K
ETIM 7	EC001449 - Device for monitoring of safety-related circuits
ETIM 8	EC001449 - Device for monitoring of safety-related circuits
ETIM 9	EC001449 - Device for monitoring of safety-related circuits
eClass	V11.0 : 27371819
UNSPSC	39122331
E-Number (Finland)	2712898
E-Number (Sweden)	3861405

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2TLA010099R0000	Sentry S30A Terminal block	Sentry S30A	1	piece
2TLA010099R0100	Sentry S30B Coding kit	Sentry S30B	1	piece
2TLA010099R0001	Sentry S30C Terminal block	Sentry S30C	1	piece

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Safety Relays → Single Function Safety Relays

Low Voltage Products and Systems → Control Products → Safety Products → Safety Relays → Single Function Safety Relays

