

Product Code: CMA630BL

Description: 13A 1 Gang Socket Outlet With Twin Earth Terminals - Blue (Medical Equipment Only)



General Information

Plate Dimensions (mm)	86 (W) x 86 (H) x 9,5 (D)
Plate Fixing Centres - Horizontal (mm)	60.3
Style	Rounded Profile
Finish	Blue
Materials	Front Plate: Urea Terminals: Brass Earth Strap: Mild Steel
Anti Microbial Certified	Yes
Rated Voltage (V~) (Ue)	250
Resistive Load Rating (A)	13
Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Switched	No
Twin Earth Terminals	Yes
Minimum Back Box Depth (mm)	25
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40
Warranty (Years)	20

Rear Housing: Urea
Terminal Screws: Steel & Yellow Passivated

Frequency (Hz) 50

Terminal Torque Value (Nm) 2

Standards BS 1363-2

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.

