Eaton 4990073FULL-0122X

Catalog Number: 4990073FULL-0122X

Eaton, Alarms & signalling devices, Fulleon, CX Mains Call Point, Weatherproof, Glass element, Single Pole Changeover contacts, Red housing, Back box.

General specifications

Product Name

Eaton Conventional call point

EAN

8054934906091

Product Height

87 mm

Product Weight

0.22 kg

Catalog Number

4990073FULL-0122X

Product Length/Depth

57 mm

Product Width

113 mm



Product specifications

Degree of protection (IP)

Product branding

Cable entry M20 hole

IP66

Eaton

Resources

Operating temperature - min Construction material ABS/FR Color Red Material Plastic System wiring 0.28 mm - 2.5 mm Humidity (Non Condensing) - Max 95 % **Number Of Poles** 1 Addressing mode Hard addressing System typology Conventional (Non-addressable) **EN Certification Standards** EN54 Pt11 (Manual Call Point) Alarm current - min 0 mA Fitted with: Glass Disc Mounting position Wall surface (internal) Wall (weatherproof) Operating temperature - max 70 °C

Resettable

No

Standby current

0

Alarm current - max

3000 mA

Type of messaging

Fire brigade alarm (red)

Humidity (Non Condensing) - Min

0 %



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2023 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia