





**Video Link : -**

**<https://youtu.be/qaMhLmCcTSM>**

## Specification

### Printing

- Extruder Quantity **2**
- Nozzle Diameter **0.4 mm**
- Maximum Extruder Temperature **240°C (464°F)**
- Print Speed **30-100mm/s**
- Maximum platform Temperature **120°C (248°F)**
- Filament Compatibility **PLA, HIPS, ABS, PVA**
- Filament Diameter **1.75mm (0.069IN)**
- Print Volume **200\*148\*150mm (7.9\*5.8\*5.9IN)**
- Layer Thickness **0.1mm-0.4mm**
- Print Precision **±0.2mm**

### Mechanical&Dimension

- Printer Dimension **526\*360\*403mm (20.7\*14.2\*15.9IN)**
- Screen **3.5-inch touch screen**
- Net Weight **14.8kg (32.63LBS)**

- Gross Weight **21kg (46.31LBS)**
- Spool **External**
- Running Noise **55dB**
- Working Environment **15-30°C (59-86°F)**

## Electrical

- Power Input **AC100-240V, 47-63Hz**
- Power **320W**
- Power Output **24V, 13.3A**
- Connectivity **USB cable, SD card**

## Software

- Software **FlashPrint**
- File Input Format **3MF / STL / OBJ / FPP / BMP / PNG / JPG / JPEG files**
- File Output Format **X3G files**