

## Product information

# 83 10 010

## Pipe Wrench 90°

DIN 5234

- Swedish pattern
- 90° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	83 10 010
EAN	4003773014188
Pliers	red powder-coated
Weight	779 g
Dimensions	310 x 57 x 19 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Clamping width	42 mm
Capacities for pipes (diameter)	Ø 1 5/8 Inch
Capacities for pipes (diameter)	Ø 42 mm
Capacities for nuts	42 mm
Inner diameter, inches	Ø 1 Inch

*technical change and errors excepted*

