

# PRODUCT DATASHEET

## SMART+ Wifi Orbis Wall Aqua IP44

### 280x160mm TW

SMART+ WIFI ORBIS WALL AQUA | Smart bathroom decorative ceiling and wall with wifi technology IP44 TW and dimmable luminaires



---

#### Areas of application

- Bathrooms

---

#### Product benefits

- Easy and quick installation

---

#### Product features

- Type of protection: IP44
- Controllable via LEDVANCE SMART+ WiFi App (with minimum Android™ 4.4 or iOS 10.0)
- Controllable via voice control available: Google Assistant or Amazon Alexa
- Adjustable color temperature via Tunable White: 3,000...6,500 K
- Dimmable
- Network protocol: WiFi



## TECHNICAL DATA

### Electrical data

Nominal wattage	12.00 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	49.000 mA
Inrush current	3.4 A
Inrush current time $T_{h50}$	100 $\mu$ s
Power factor $\lambda$	> 0.90
Total harmonic distortion	< 20 %
Protection class	II
Operating mode	External LED driver

### Photometrical data

Luminous flux	1000 lm
Total luminous flux of contained light sources	1200 lm
Luminous efficacy	90 lm/W
Color temperature	3000...6500 K
Light color (designation)	Tunable White
Color rendering index Ra	> 80
Standard deviation of color matching	< 6 sdcn
Photobiological safety group acc. to EN62778	RG0
Photobiological safety group acc. to EN62471	RG0
Beam angle	110 °

### Dimensions & Weight

Length	280.00 mm
Width	160.00 mm
Height	94.00 mm
Product weight	720.00 g

## Materials & Colors

Product color	White
Housing color	White
Body material	Steel
Cover material	Polycarbonate (PC)
Mercury content	0.0 mg

## Application & Mounting

Ambient temperature range	-20...+40 °C
Temperature range at storage	-20...+80 °C
Type of connection	Screw terminal
Type of protection	IP44
Protection class IK (shock resistance)	IK03
Dimmable	Yes
Type of dimming	WiFi
Mounting type	Surface
Mounting location	Ceiling
Application environment	Indoor
LED module replaceable	Not replaceable
With light source	Yes

## Lifespan

Lifespan L70/B50 at 25 °C	30000 h
Number of switching cycles	15000

## Emergency lighting

Type of emergency operation test	None
Integrated test switch	No

## Certificates & Standards

Standards	CE / UKCA
Luminaire with limited surface temperature, "D sign"	No

## EQUIPMENT / ACCESSORIES

- Mounting bracket included
- Mounting screws and dowels included
- Control via app or voice control requires compatible Smart home system
- For control via LEDVANCE SMART + WiFi App, a smart phone or Tablet PC is required

## DOWNLOAD DATA

## Documents and certificates



User instruction



Declarations Of Conformity CE



Declarations Of Conformity UKCA

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075574359	Folding box 1	202 mm x 104 mm x 332 mm	875.00 g	6.97 dm <sup>3</sup>
4058075574366	Shipping box 4	346 mm x 220 mm x 420 mm	4447.00 g	31.97 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.