

## PRODUCT DATASHEET

# Conversion kit + SubstiTUBE T5 AC HO54 26 W/4000 K 1149.00 mm

SubstiTUBE T5 Conversion Kit single lamp | T5 LED tubes including conversion kit for single lamp luminaires



### Areas of application

- Offices, public buildings
- Supermarkets and department stores
- Industry
- General illumination within ambient temperatures from -20...+45 °C

### Product benefits

- Only around 5 minutes per luminaire needed for rewiring
- No ECG compatibility issues
- No ECG maintenance necessary
- No bending thanks to glass technology
- Shatter protection thanks to special PET coating
- High luminous flux for sophisticated lighting tasks

### Product features

- Contains 10 SubstiTUBE T5 220-240V AC LED tubes and 10 conversion kits for single-lamp luminaires
- Conversion kit contains all necessary material for conversion of ECG luminaires to AC mains
- Detailed step-by-step instruction for guaranteed TÜV-certification available
- LED replacement for T5 fluorescent lamps with G5 base on AC mains
- Lamp tube made of glass with splinter protection e.g. for food industry applications



- High color consistency:  $\leq 5$  SDCM
- Lifetime: up to 50,000 h
- Low flicker according to EU 2019/2020
- Type of protection: IP20

---

## TECHNICAL DATA

### Dimensions & Weight

Product weight	1900.00 g
----------------	-----------

### Additional product data

Product remark	This product contains the following LED Tube as a light source: SubstiTUBE T5 AC HO54 26 W/4000 K 1149.00 mm, EAN: 4058075543409, LED tube EEC: D / EPREL ID LED Tube: 642843
----------------	---

### Certificates & Standards

Type of protection	IP20
--------------------	------

### Country-specific categorizations

Order reference	LEDTUBE T5 AC H
-----------------	-----------------

---

### Safety advice

- Operation in outdoor applications in suitable damp-proof luminaires possible according to data sheet and installation instruction.
- Not suitable for operation with electronic control gear.

---

## DOWNLOAD DATA

### Documents and certificates



Installation guide

---

## References / Links

- For current information see [www.ledvance.com/substitube](http://www.ledvance.com/substitube)

---

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.