

Technical Specification



2 Gang Blank Plate Product Code: SFBK061 Description:



General Information

Insert Dimensions (mm) 142.5 (W) x 82.5 (H) x 2.5 (D) Plate Dimensions (mm) $146 \text{ (W)} \times 86 \text{ (H)} \times 4 \text{ (D)}$

Plate Fixing Centres - Horizontal (mm) 120.6

Style Screwless Complete Finish Matt Black (RAL 9011)

SCP061# Compatible Cover Plate

> Cover Plate: Polycarbonate Materials

> > Terminals: Brass

Earth Strap: Mild Steel

Anti Microbial Certified

Minimum Back Box Depth (mm)

Ingress Protection IP20

Operational Temperature (°C) -5 to +40

Warranty (Years) 10

Standards BS 5733 Insert: Polycarbonate

Terminal Screws: Steel & Yellow Passivated

Additional Information For cleaning / polishing of products, use only a soft, dry, clean cloth.

This outlet is not continuously rated and therefore not suitable for use as a permanent charging outlet. CLICK dual voltage shaver outlets incorporate a double wound isolating transformer rated 20Va at 230V or 115V and meets BS EN 61558-2-5:2010 making it safe for use in bathrooms.

PTC resettable fuses increase resistance as temperature increases due to increased flow. PTC resettable fuses are designed to limit unsafe currents while allowing constant safe current levels, resistance will "reset" automatically when the fault is removed and temperature returns to a safe level. Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram

with the relevant product.

Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.







