

NEBO[®]

MINI LARRY[®] 500

LIGHT MODES

- Flashlight High (500 lumens): 1 hour / 126 meters
- Flashlight Low (220 lumens): 4 hours / 80 meters
- Work Light High (450 lumens): 1 hour / 30 meters
- Work Light Low (240 lumens): 4.5 hours / 20 meters

DESIGN

- USB-C rechargeable
- Smart Power Control[™] (SPC)
- Removable dual-direction steel clip
- Powerful magnetic base
- Waterproof (IP67)
- Anodized aircraft-grade aluminum

OPERATION

- Front-positioned button

ACCESSORIES

- USB-A to USB-C charging cable

BATTERIES

- Powered by internal lithium-ion rechargeable battery (14500, 3.7V, 800mAh) (Recharge time: 2 hours)

SPECS

- 0.2 lb.
- (H) 4.19" x (W) 1.34" x (D) 0.94"



Actual Size



RECHARGEABLE

COMPACT SIZE POWERFUL LIGHT

The Mini Larry 500 may be small, but it packs a big punch with its **500 lumen flashlight** and **450 lumen C-O-B work light**. This compact light is **waterproof, USB-C rechargeable**, and features a **dual-direction clip** and **magnetic base** to provide convenient hands-free lighting solutions.

UPC CODE	ITEM	CASE
645397940630	NEB-POC-1004	12

PDQ Dimensions
(H) 12.36" x (W) 6.3" x (D) 13.9"
Natralock Dimensions
(H) 8.27" x (W) 4.88" x (D) 1.5"

