

Eaton AN56AN0AC

Catalog Number: AN56AN0AC

Eaton Freedom NEMA motor control starter, 1/3 hp at 115V,1 hp at 230V, 1-1/2 hp at 208,240V, 2 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 9A, Three-pole

General specifications

Product Name

Eaton Freedom NEMA motor control starter

Catalog Number

AN56AN0AC

UPC

782113972466

Product Length/Depth

4.61 in

Product Height

3.31 in

Product Width

4.38 in

Product Weight

2.6 lb

Warranty

Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Heater Packs must be purchased separately



Product specifications

Size

0

Coil voltage

110-120 Vac, 50/60 Hz

HP rating - max

1/3 hp at 115V, 1 hp at 230V, 1-1/2 hp at 208, 240V, 2 hp at 480, 600V

Phase

Single-phase, three-phase

Amperage Rating

9A

Number of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Drawings

[AN56AN0_C 2D Drawing Xchange](#)

[AN56AN0_C AutoCAD 2D Footprint \(mm\)](#)

[AN56AN0_C AutoCAD 2D Footprint](#)

[AN56AN0_C 2D PDF](#)

[AN56AN0_C 3D Inventor](#)

[AN56AN0_C 3D Model Xchange](#)

Specifications and datasheets

[Quick Selector - NEMA Contactors](#)

[Eaton Specification Sheet - AN56AN0AC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia