

Technical Specification

Product Code: CMA20401

Description: 1 Gang GridPro® Frontplate



General Information

Plate Dimensions (mm)	86 (W) x 86 (H) x 9 (D)	
Plate Fixing Centres - Horizontal (mm)	60.3	
Style	Mode	
Finish	Polar White	
Materials	Front Plate: Urea	Fixing Lugs: Brass
Anti Microbial Certified	Yes	
Yoke Required	No	
Minimum Back Box Depth (mm)	25	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	

Standards BS 5733

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.
All white moulded accessories are manufactured using Urea Formaldehyde, which has similar inherent properties to antimicrobial additives that inhibit the growth of infectious diseases as well as anti-viral properties against enveloped and non-enveloped viruses.
All products have been independently tested with 99.9% of enveloped viruses and 92% of non-enveloped viruses killed off whilst achieving a 99.9% kill rate across all four types of the strains of bacteria - MRSA, E-Coli, Salmonella, and Klebsiella Pneumoniae.