


Technical Specification

Product Code: VPSC20509

Description: 9 Gang GridPro® Frontplate



General Information

Plate Dimensions (mm)	146 (W) x 206 (H) x 8 (D)
Dimensions With Gasket (mm)	149 (W) x 209 (H) x 9 (D)
Style	Deco
Finish	Satin Chrome
Gasket Colour	Supplied With Both Black & White Gasket
Materials	Cover Plate: Stainless Steel
Anti Microbial Certified	No
Yoke Required	Yes (3 x GR20400)
Minimum Back Box Depth (mm)	47
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40
Warranty (Years)	10

Standards BS 5733

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.
Requires 3 x GR20400 Yokes & WA518 Back Box

UK Design Registration: 3015621

Scolmore House, Mariner, Lichfield Road Industrial Estate,
Tamworth, Staffordshire, B79 7UL United Kingdom
T: +44 (0)1827 63454 | **F:** +44 (0)1827 63362
E: sales@scolmore.com | **W:** scolmore.com

**UK
CA**

