

Technical Specification

Product Code: GM050BK

Description: 1 Module Dimmer Mounting Kit



General Information

Dimensions (mm)	24.5 (W) x 50 (H)	
Finish	Black	
Insert Colour	Black	
Materials	Body & Insert: Nylon	Control Button: Nylon
Anti Microbial Certified	No	
Minimum Back Box Depth (mm)	47	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	

Standards BS 5733

Additional Information For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.

Compatible Dimmer Modules MD9014: 100W Dual Mode LED Dimmer Module
MD9001: 6A Push ON/OFF (Dummy Dimmer / Non Dimmable) Module
MD9010: 1-10V Analogue Rotary Dimmer Module
MD9022: 40-250W Leading Edge Dimmer Module
MD9042: 60-400W Leading Edge Dimmer Module

UK Patent: GB 2578427

Scolmore House, Mariner, Lichfield Road Industrial Estate,
Tamworth, Staffordshire, B79 7UL United Kingdom
T: +44 (0)1827 63454 | **F:** +44 (0)1827 63362
E: sales@scolmore.com | **W:** scolmore.com

**UK
CA**

