

Technical Specification

Product Code: GM2001BK

Description: 20AX 1 Way Switch Module



General Information

Dimensions (mm)	24.5 (W) x 50 (H) x 22.5 (D)		
Finish	Black		
Insert Colour	Black		
Switch Finish	Black		
Materials	Body & Insert: Nylon		Switch: Urea
	Terminals: Brass		Terminal Screws: Steel & Yellow Passivated
	Contacts: Silver "on-lay" Copper / Brass		
Anti Microbial Certified	No		
Rated Voltage (V~) (Ue)	250	Frequency (Hz)	50
Inductive Load Rating (AX)	20		
Load Rating Comments	Suitable for Inductive Loads		
Termination Type	Screw		
Terminal Size (mm)	Ø5	Terminal Torque Value (Nm)	1.2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4		
1 Way Switch	Yes		
Minimum Back Box Depth (mm)	25 (35 Flat Plate)		
Ingress Protection	IP20		
Operational Temperature (°C)	-5 to +40		
Warranty (Years)	10		

Standards BS EN 60669-1

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.

UK Patent: GB 2578427

Scolmore House, Mariner, Lichfield Road Industrial Estate,
Tamworth, Staffordshire, B79 7UL United Kingdom
T: +44 (0)1827 63454 | **F:** +44 (0)1827 63362
E: sales@scolmore.com | **W:** scolmore.com

