

Technical Specification

Product Code: GM2003BK

Description: 20AX 2 Way Keyswitch Module



General Information

Dimensions (mm)	24.5 (W) x 50 (H) x 22.5 (D)	
Finish	Black	
Insert Colour	Black	
Materials	Body & Insert: Nylon	Switch: Nylon
	Terminals: Brass	Terminal Screws: Steel & Yellow Passivated
	Contacts: Silver "on-lay" Copper / Brass	
Anti Microbial Certified	No	
Rated Voltage (V~) (Ue)	250	Frequency (Hz) 50
Inductive Load Rating (AX)	20	
Load Rating Comments	Suitable for Inductive Loads	
Termination Type	Screw	
Terminal Size (mm)	Ø5	Terminal Torque Value (Nm) 1.2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4	
2 Way Switch	Yes	
Keyswitch	Yes	
Minimum Back Box Depth (mm)	25 (35 Flat Plate)	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	

Standards BS EN 60669-1

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.

UK Patent: GB 2578427

Scolmore House, Mariner, Lichfield Road Industrial Estate,
Tamworth, Staffordshire, B79 7UL United Kingdom
T: +44 (0)1827 63454 | **F:** +44 (0)1827 63362
E: sales@scolmore.com | **W:** scolmore.com

