

Technical Specification

Product Code: GM2018NBK-BL

Description: 20AX Double Pole Switch With Neon Module



General Information

Dimensions (mm)	24.5 (W) x 50 (H) x 22.5 (D)		
Finish	Black		
Insert Colour	Black		
Switch Finish	Black		
Materials	Body & Insert: Nylon	Switch: Urea	
	Neon Lens: Polycarbonate	Terminals: Brass	
	Terminal Screws: Steel & Yellow Passivated	Contacts: Silver "on-lay" Copper / Brass	
Anti Microbial Certified	No		
Rated Voltage (V~) (Ue)	250	Frequency (Hz)	50
Inductive Load Rating (AX)	20		
Load Rating Comments	Suitable for Inductive Loads		
Termination Type	Screw		
Terminal Size (mm)	Ø5	Terminal Torque Value (Nm)	1.2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4		
Double Pole Switch	Yes		
Neon Indicator	Yes	Indicator Colour	Red
Product Marking	Boiler		
Minimum Back Box Depth (mm)	25 (35 Flat Plate)		
Ingress Protection	IP20		
Operational Temperature (°C)	-5 to +40		
Warranty (Years)	10		

Standards BS EN 60669-1

Additional Information For cleaning / polishing of products, use only a soft, dry, clean cloth. Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product. Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.

UK Patent: GB 2578427

Scolmore House, Mariner, Lichfield Road Industrial Estate,
Tamworth, Staffordshire, B79 7UL United Kingdom
T: +44 (0)1827 63454 | F: +44 (0)1827 63362
E: sales@scolmore.com | W: scolmore.com

