

Technical Specification

Product Code: GM2080BK
 Description: 240V~ Red Indicator Module



General Information

Dimensions (mm)	24.5 (W) x 50 (H) x 22.5 (D)	
Finish	Red	
Insert Colour	Black	
Materials	Body & Insert: Nylon	Neon Lens: Polycarbonate
	Terminals: Brass	Terminal Screws: Steel & Yellow Passivated
Anti Microbial Certified	No	
Rated Voltage (V~) (Ue)	250	Frequency (Hz) 50
Termination Type	Screw	
Terminal Size (mm)	Ø5	Terminal Torque Value (Nm) 1.2
Terminal Capacity - Solid (mm²)	3 x 2.5, 2 x 4	
Neon Indicator	Yes	Indicator Colour Red
Minimum Back Box Depth (mm)	25 (35 Flat Plate)	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	
Standards	BS 5733	

Additional Information	For cleaning / polishing of products, use only a soft, dry, clean cloth. Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product. Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.
------------------------	--

UK Patent: GB 2578427

Scolmore House, Mariner, Lichfield Road Industrial Estate,
 Tamworth, Staffordshire, B79 7UL United Kingdom
 T: +44 (0)1827 63454 | F: +44 (0)1827 63362
 E: sales@scolmore.com | W: scolmore.com

