

Technical Specification

Product Code: GM2405BK
 Description: Satellite (F Type) Module



General Information

Dimensions (mm)	24.5 (W) x 50 (H) x 20 (D)	
Finish	Black	
Materials	Front Cover: Nylon Terminal: Brass Fixing Screw: Nickel Plated Steel	Housing: Aluminium Terminal Screw: Brass
Anti Microbial Certified	No	
Termination Type	Screw	
Isolated	No	
Non-Isolated	Yes	
Non-Isolated Comments	Enables 2 way signal transmission	
Shielded	Yes	
Minimum Back Box Depth (mm)	25 (35 Flat Plate)	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	10	Warranty - Electronics (Years) 1

Additional Information
 For cleaning / polishing of products, use only a soft, dry, clean cloth.
 Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
 Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.

UK Patent: GB 2578427

Scolmore House, Mariner, Lichfield Road Industrial Estate,
 Tamworth, Staffordshire, B79 7UL United Kingdom
T: +44 (0)1827 63454 | **F:** +44 (0)1827 63362
E: sales@scolmore.com | **W:** scolmore.com



DoC



Installation

