

Technical Specification

Product Code: GMg001
 Description: 6A 2 Way Push On/Off (Non-Dimmable) Module



General Information

|                                 |                          |                                     |
|---------------------------------|--------------------------|-------------------------------------|
| Dimensions (mm)                 | 25 (W) x 62 (H) x 22 (D) |                                     |
| Materials                       | Body: Nylon              | Terminals: Brass                    |
|                                 | Terminal Screws: Brass   | PCB: Multiple Electronic Components |
| Rated Voltage (V~) (Ue)         | 230                      | Frequency (Hz) 50                   |
| Resistive Load Rating (A)       | 6                        |                                     |
| Termination Type                | Screw                    |                                     |
| Terminal Size (mm)              | Ø2.8                     | Terminal Torque Value (Nm) 0.2      |
| Terminal Capacity - Solid (mm²) | 2 x 1.5                  |                                     |
| 2 Way Switch                    | Yes                      |                                     |
| Dimmer Technology Type          | None (On & Off Only)     |                                     |
| Minimum Back Box Depth (mm)     | 25 (35 Flat Plate)       |                                     |
| Operational Temperature (°C)    | -5 to +40                |                                     |
| Warranty (Years)                | 1                        |                                     |
| Standards                       | BS EN 60669-1            |                                     |

|                        |                                                                                                                                                                                                                                                                                                                                   |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Additional Information | For cleaning / polishing of products, use only a soft, dry, clean cloth.<br>Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.<br>Due to the housing height, the module cannot be mounted directly above another on a multi-tier mounting plate. |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|