



## Main

Range	Spacial
Product name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	23.62 in (600 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	7.87 in (200 mm)
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door 1 lock
Door type	Glass
Mounting plate description	Without mounting plate

## Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body steel Door steel and security glass
Surface finish	Epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	UL CUL DNV-GL
Product Weight	28.99 lb(US) (13.148 kg)

## Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK08 IEC 62262

## Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480212000
Returnability	No
Country of origin	ES

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.41 in (62.0 cm)
Package 1 Width	24.41 in (62.0 cm)
Package 1 Length	8.66 in (22.0 cm)
Package 1 Weight	28.99 lb(US) (13.148 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------