



### Main

|                                    |                                                                                                                |
|------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Range                              | Spacial                                                                                                        |
| Product or Component Type          | Cable gland plate                                                                                              |
| Accessory / separate part category | Cable management accessory                                                                                     |
| Anwendung                          | Multi-purpose                                                                                                  |
| Range compatibility                | Spacial (Spacial SF)                                                                                           |
| Mounting Location                  | Enclosure bottom                                                                                               |
| Cable gland type                   | Standard                                                                                                       |
| Cable entry                        | 1 entry                                                                                                        |
| Device composition                 | Fixing elements<br>1 plate<br>Self extinguishing polyurethane adhesive gasket with cross-section of 15 x 25 mm |
| Quantity per Set                   | Set of 1                                                                                                       |
| Material                           | Galvanised steel                                                                                               |

### Complementary

|           |                                                       |
|-----------|-------------------------------------------------------|
| Height    | 0.98 in (25 mm)                                       |
| Width     | Nominal 31.50 in (800 mm)<br>Useful 24.25 in (616 mm) |
| Depth     | Nominal 19.69 in (500 mm)                             |
| Thickness | 0.06 in (1.5 mm)                                      |

### Ordering and shipping details

|                   |                                     |
|-------------------|-------------------------------------|
| Category          | 80036-ENCLOSURE SYSTEMS ACCESSORIES |
| Discount Schedule | ES1                                 |
| GTIN              | 3606485126296                       |
| Returnability     | No                                  |
| Country of origin | FR                                  |

### Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 1.00 in (2.54 cm)    |
| Package 1 Width              | 9.60 in (24.38 cm)   |
| Package 1 Length             | 25.70 in (65.28 cm)  |
| Package 1 Weight             | 7.94 lb(US) (3.6 kg) |

### Offer Sustainability

|                          |                                                                                                                                                                                      |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product                                                                                                                                                                |
| REACH Regulation         |  <a href="#">REACH Declaration</a>                                                                |
| REACH free of SVHC       | Yes                                                                                                                                                                                  |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Mercury free             | Yes                                                                                                                                                                                  |

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>         |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|