

Product Code: QEC15-9

Description: Earth Bonding Clamps EC15 Wet Conditions

**Dimensions**

Length (mm)	240
Width (mm)	40
Depth (mm)	15
Suitable Pipe Diameter (mm)	32 - 50

General Information

Conductor Size (mm²)	2.5 - 10
Temperature Rating (°C)	-35 to +105

Materials

Strap: Stainless Steel
Clamp Housing: Stainless Steel
Cable Tag, Fixing Screws & Locking Nut: Brass
Safety Label: Aluminium

Standards

BS 951: 2009

