

Travel A/V adapter: 3-in-1 Mini DisplayPort to DisplayPort DVI or HDMI converter

Product ID: MDP2DPDVHD



The MDP2DPDVHD mini DisplayPort to DisplayPort, DVI or HDMI Multifunction Adapter converts a mini DisplayPort (mDP) input to DisplayPort, DVI or HDMI output signals - all in a single compact adapter.

This multifunction adapter offers the unique ability to connect almost any display to your mini DisplayPort equipped PC or Mac, providing the perfect solution for business environments that have mixed display hardware - saving the expense of purchasing new displays for compatibility. This Mini DisplayPort adapter is the perfect accessory for any of your MacBook or Microsoft Surface Pro devices with mDP.

A plug-and-play solution that requires no software or drivers, this versatile mDP adapter offers a quick and simple installation for the utmost convenience.

Compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port.

This adapter allows for audio pass-through if supported by the video source. Please review the video source manual to confirm support.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

- Use your existing DVI, HDMI or DisplayPort monitors with a new mini DisplayPort device
- Perfect for IT professionals seeking a solution for connecting mixed display hardware to mini DisplayPort computers

Features

- Adapt Mini DisplayPort to DisplayPort, HDMI or DVI
- Supports resolutions up to 2560x1600 using DisplayPort, 1920x1200 using HDMI/DVI
- No software/drivers required
- Compact design
- Compatible with Intel Thunderbolt

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DisplayPort - 1.2 HDMI - 1.4 DVI-D - Single-Link
Audio	Yes

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Digital Resolutions	DisplayPort: 2560x1600 DVI/HDMI; 1920x1200
Audio Specifications	DisplayPort - 5.1 Channel Audio HDMI - 7.1 Channel Audio DVI - No Audio Support

Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
-------------	-------------------------------

Connector B	1 - DisplayPort (20 pin)
	1 - DVI-D (25 pin)
	1 - HDMI (19 pin)

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85%RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	5.9 in [150 mm]
Product Length	10.0 in [25.4 cm]
Product Width	1.7 in [4.4 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	1.7 oz [49.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.7 in [1.7 cm]
Shipping (Package) Weight	2.0 oz [57.0 g]

What's in the Box

Included in Package	1 - MDP to DP/DVI/HDMI Adapter
---------------------	--------------------------------

**Product appearance and specifications are subject to change without notice.*