

CR-Scan Ferret

Small Build, Great Capture



Compact Design



Dual Mode Scanning



ASIC Chipset

[Join the group](#)



Eight advantages



Affordable



Compact design



Dual mode scanning



ASIC chipset



Full color scanning



Easy operation



Outdoor scanning



Low power consumption

Product Parameters

Product Name: **CR-Scan Ferret**

Accuracy: **0.1mm**

Resolution/Point Distance: **0.16mm**

Single capture range: **560*820mm@700mm**

Working Distance: **150~700mm**

Minimum Scanning: **50*50*50mm**

Frame Rate/Scan Speed: **up to 30 fps**

Light Source: **NIR**

Outdoor Scanning: **Support Scanning in Bright Sunlight**

Tracking Mode: **Visual Tracking**

Color Texture: **Support**

Alignment: **feature/marker/color**

Machine Weight: **105g**

Output Format: **OBJ / STL / PLY**

Connection Mode: **USB 3.0/2.0**

Machine Size: **120*30*26mm**

Compatible System: **Android / Win 10/11 (64-bit) / * Mac OS** * Launched in June 2023